■ POWER SUPPLY

Wall mount type


(input:AC 100~240V,50/60Hz,output: DC 12V/1A) OR

Built-in type *For dental unit

(input: AC 20~30V,50/60Hz, output: DC 12V/1.25A)



Optional Accessories





FINE VISION ELECTRONICS CO.,LTD.

11/F.,NO 123-8,HSING TE RD., SANCHUNG CITY,TAIPEI COUNTY TAIWAN R.O.C.

TEL:886-2-85123668 FAX:886-2-85123678

Web Site: www.finevision.com.tw E-mail: info@finevision.com.tw





High intensity output

super high luminosity LED in the world



The ULight[™] is offered with a super high luminosity LED. The light wavelength is between 440nm and 480nm and the intensity is more than 1000mW/cm². It is an applicable tool. The ULight[™] can work effectively within almost photosensitive polymerized composites.



Never shutdown

If the temperature become too high due to continuous use, it will change to safe mode automatically and never shutdown.

Germproof progress

keep it clean always



Lid Lid Might"

The ULight[™] is used by the germproof material in the plastic cover. It can avoid the infection caused by bacteria or viruses effectively. It can also take care of the users' health easily.

Simply Operate

fully function on two colors indication LED

5s 🔾

Just one button and simply to operate Fully function on two colors indication LED

10s 🔾

Built-in thermal protection

15s \bigcirc | 15s

Keep it safty and long lifetime.

Multi-curing timer

This function provides you with 3 kinds of the timer format to be selected.

•5 sec •10 sec •15 sec


Multi-curing output mode

This function provides you with different operation modes to be selected









WAVE LENGTH (nm)